







STANDARD VINYL



Super Heavy Duty 450 lbs, Capacity, 3" High Resilient Density Foam for Better Comfort, Rubber Edge Banding Protection on Seat & Back Upholstery Type Height Seat Dimensions Back Dimensions Footring Base Caster Adjustment

	AM20M-V	Vinyl	21"-31"	20" W x 18" D	16" W x 16" H	20"	Polished Aluminum	1
	AM22M-V	Vinyl	17"-22"	20" W x 18" D	16" W x 16" H		Polished Aluminum	1
	PM20M-V	Vinyl	21"-31"	20" W x 18" D	16" W x 16" H	20"	Black Nylon	1
	PM22M-V	Vinyl	17"-22"	20" W x 18" D	16" W x 16" H		Black Nylon	1
OLOR OPTIONS								
*PreFixx Group II*								

• Meets or Exceeds California Tech Bulletin 117, Boston Fire Dept. IX-1, • Federal Standard A-A-2950, • UFAC Fabric Class 1, • FMVSS-302

	Blue-211	Navy-221	Burgundy-261	Black-251	Grey-231	Grey-232	Grey-233
MECHANISN	M OPTIONS	S					
WECHANISM	I OPTIONS	5					

• 100 Vinyl Face, Poly/cotton Backing, • Protective Coating for Increased Stain Resistence, • Abrasion 400,000 Double Rubs



	DLC
Controls	Description
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height
ST	Height and Seat and Back Tilt (This control has two levers, one for height adjustment and the other for Seat

	DLC
Controls	Description
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height a
ST	Height and Seat and Back Tilt ( This control has two levers, one for height adjustment and the other for Seat back height with knob

	DLC
Controls	Description
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height a
ST	Height and Seat and Back Tilt ( This control has two levers, one for height adjustment and the other for Seat a back height with knob
FLC	Three Lever for Individual Lift ( Height lever adjustment, seat tilt adjustment back tilt adjustment and height land a seat tension knob

Controls	Description
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height a
ST	Height and Seat and Back Tilt ( This control has two levers, one for height adjustment and the other for Seat a back height with knob
FLC	Three Lever for Individual Lift ( Height lever adjustment, seat tilt adjustment back tilt adjustment and height and a seat tension knob
FOOTRING OPTIONS	

	1			
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height a			
ST	Height and Seat and Back Tilt ( This control has two levers, one for height adjustment and the other for Seat back height with knob			
FLC Three Lever for Individual Lift ( Height lever adjustment, seat tilt adjustment back tilt adjustment and and a seat tension knob				
FOOTRING OPTIONS				

FOOTRING OPTIONS	
FLC	Three Lever for Individual Lift ( Height lever adjustment, seat tilt adjustment back tilt adjustment and height back adjustment with knob and a seat tension knob
ST	Height and Seat and Back Tilt (This control has two levers, one for height adjustment and the other for Seat and Back tilt adjustment and back height with knob
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height adjustment with knob
Controls	Description

ST	Height and Seat and Back Tilt ( This control has two levers, one for height adjustment and the other for Seat a back height with knob
FLC	Three Lever for Individual Lift ( Height lever adjustment, seat tilt adjustment back tilt adjustment and height and a seat tension knob
FOOTRING OPTIONS	

	FR04
Footring	Description
FR04	Knobless Nylon Footring 18" The Footring is Loosened and Tightened by Turning the Outer Ring. (option for models 20S, 45, 50 and 60)
FR05	Knobless Aluminum with Steel Ring 20" The Footring is Loosened and Tightened by Turning the Outer Ring. (option for models 10, 20M and 20W)
FR06	Nylon Center with Steel Ring, Footring 18" (option for models 20S, 45, 50 and 60)
ARM REST	OPTIONS
	TF TA TAA

Arms	Description	
TF	Fixed Height and Width, Black	
TA	Fixed Height and Adjustable Width, Black	
TAA	Adjustable Height and Adjustable Width	
CASTER OF	PTIONS	
		2

Description


Braking Caster , Recommended where Chairs may roll to easily when is Not Occupied

Soft Urethane Braking Caster, Recommended for reduce Mobility when is Not Occupied

Soft Urethane Caster, Recommended on Tile, Cement and other Hard Surfaces

Nylon Glide, Recommended for use in areas where requiring limited mobility

20M SERIES	STANDARD VINYL
	INDUSTRIAL SEATING, INC. (800) 486-9666



Super Heavy Duty 450 lbs, Capacity, 3" High Resilient Density Foam for Better Comfort, Rubber Edge Banding Protection on Seat & Back

20" W x 18" D

Seat Dimensions Back Dimensions Footring

15" W x 12" H

20"

Base

Polished

Caster

**FOOTRING OPTIONS** 

FR06

TA TAA

Caster

1B

1U

1UB

AE20M-V

Vinyl

Vinyl

Vinyl

Vinyl

Upholstery Type Height

**FR04** 

Knobless Aluminum with Steel Ring 20"

Knobless Nylon Footring 18"

Description

Description

Fixed Height and Width, Black

Fixed Height and Adjustable Width, Black

Adjustable Height and Adjustable Width

Footring FR04

FR05

Arms TF

TA

TAA

**CASTER OPTIONS** 

Adjustment 21"-31"

17"-22"

21"-31"

17"-22"

Model

AE20M-V

AE22M-V

PE20M-V

PE22M-V

**COLOR OPTIONS** 

2

**CASTER OPTIONS** 

AL20M-V

Vinyl

Upholstery Type Height

Adjustment 21"-31"

Model

 $\underline{\text{AL20M-V}}$ 

Caster

1B 1U

1UB

2



	DLC ST FLC
Controls	Description
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height adjustment with knob
ST	Height and Seat and Back Tilt (This control has two levers, one for height adjustment and the other for Seat and Back tilt adjustment and back height with knob
FLC	Three Lever for Individual Lift ( Height lever adjustment, seat tilt adjustment back tilt adjustment and height back adjustment with knob and a seat tension knob



Nylon Center with Steel Ring, Footring 18" (option for models 20S, 45, 50 and 60)

Fixed Height and Adjustable Width, Black

Description

Braking Caster , Recommended where Chairs may roll to easily when is Not Occupied

Soft Urethane Braking Caster, Recommended for reduce Mobility when is Not Occupied

**20**M SERIES

Soft Urethane Caster, Recommended on Tile, Cement and other Hard Surfaces

Nylon Glide, Recommended for use in areas where requiring limited mobility

Adjustable Height and Adjustable Width



1UB

PE20M-V

Base

Polished Aluminum Polished

Aluminum Black Nylon

Black Nylon

STANDARD VINYL

Caster

1

AE22M-V	INDUSTRIAL SEATING, INC. (800) 486-9666

Super Heavy Duty 450 lbs, Capacity, 3" High Resilient Density Foam for Better Comfort, Rubber Edge Banding Protection on Seat & Back

Seat Dimensions Back Dimensions Footring

19" W x 16.5" H 20"

19" W x 16.5" H 20"

19" W x 16.5" H

19" W x 16.5" H

20" W x 18" D

\*PreFixx Group II\*

• Meets or Exceeds California Tech Bulletin 117, Boston Fire Dept. IX-1, • Federal Standard A-A-2950, • UFAC Fabric Class 1, • FMVSS-302

• 100 Vinyl Face, Poly/cotton Backing, • Protective Coating for Increased Stain Resistence, • Abrasion 400,000 Double Rubs



	DLC ST FLC
Controls	Description
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height adjustment with knob
ST	Height and Seat and Back Tilt (This control has two levers, one for height adjustment and the other for Seat and Back tilt adjustment and back height with knob
FLC	Three Lever for Individual Lift ( Height lever adjustment, seat tilt adjustment back tilt adjustment and height back adjustment with knob and a seat tension knob
FOOTRING OPTIONS	

FR06	Nylon Center with Steel Ring, Fo	potring 18" (option for models 20S, 45, 50 and 60)	
ARM REST	OPTIONS		
	TF	TA	TAA

The Footring is Loosened and Tightened by Turning the Outer Ring. (option for models 20S, 45, 50 and 60)

The Footring is Loosened and Tightened by Turning the Outer Ring. (option for models 10, 20M and 20W)

Caster Description  1B Braking Caster, Recommended where Chairs may roll to easily when is Not Occupied  1U Soft Urethane Caster, Recommended on Tile, Cement and other Hard Surfaces  1UB Soft Urethane Braking Caster, Recommended for reduce Mobility when is Not Occupied			
1U Soft Urethane Caster, Recommended on Tile, Cement and other Hard Surfaces	Caster	Description	
	1B	Braking Caster, Recommended where Chairs may roll to easily when is Not Occupied	
1UB Soft Urethane Braking Caster, Recommended for reduce Mobility when is Not Occupied	1U	Soft Urethane Caster, Recommended on Tile, Cement and other Hard Surfaces	
	1UB	Soft Urethane Braking Caster, Recommended for reduce Mobility when is Not Occupied	
Nylon Glide, Recommended for use in areas where requiring limited mobility	2	Nylon Glide, Recommended for use in areas where requiring limited mobility	