	20S SERIES	STANDARD VINYL
	AM22S-V	<image/> <image/>
Super Heavy Duty 450 lbs, Capacity, 2	.5" High Resilient Density Foam	for Better Comfort, Rubber Edge Banding Protection on Seat &

	Model	Upholstery Type	Height Adjustment	Seat Dimensions	Back Dimensions	Footring	Base	Caster
:	<u>AM20S-V</u>	Vinyl	21"-31"	18" W x 18" D	16" W x 16" H	18"	Polished Aluminum	1
	AM22S-V	Vinyl	17"-22"	18" W x 18" D	16" W x 16" H	NO	Polished Aluminum	1
	<u>PM20S-V</u>	Vinyl	21"-31"	18" W x 18" D	16" W x 16" H	18"	Black Nylon	1
	PM22S-V	Vinyl	17"-22"	18" W x 18" D	16" W x 16" H	NO	Black Nylon	1

COLOR OPTIONS

PreFixx Group II

• 100 Vinyl Face, Poly/cotton Backing, • Protective Coating for Increased Stain Resistence, • Abrasion 400,000 Double Rubs • Meets or Exceeds California Tech Bulletin 117, Boston Fire Dept. IX-1, • Federal Standard A-A-2950, • UFAC Fabric Class 1, • FMVSS-302

Blue-211	Navy-221	Burgundy-261	Black-251	Grey-231	Grey-232	Grey-233

MECHANISM OPTIONS







Controls	Description
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height adjustment with knob
ST	Height and Seat and Back Tilt (This control has two levers, one for height adjustment and the other for Seat and Back tilt adjustment and back height with knob
FLC	Three Lever for Individual Lift (Height lever adjustment, seat tilt adjustment back tilt adjustment and height back adjustment with knob and a seat tension knob

FOOTRING OPTIONS



Footring	Description
FR04	Knobless Nylon Footring 18" The Footring is Loosened and Tightened by Turning the Outer Ring. (option for models 208, 45, 50 and 60)
FR05	Knobless Aluminum with Steel Ring 20" The Footring is Loosened and Tightened by Turning the Outer Ring. (option for models 10, 20M and 20W)
FR06	Nylon Center with Steel Ring, Footring 18" (option for models 20S, 45, 50 and 60)



2

	B THE STATE OF THE						
Caster	Description						
1B	Braking Caster, Recommended where Chairs may roll to easily when is Not Occupied						
1U	Soft Urethane Caster, Recommended on Tile, Cement and other Hard Surfaces						
1UB	Soft Urethane Braking Caster, Recommended for reduce Mobility when is Not Occupied						

AL20S-V



Nylon Glide, Recommended for use in areas where requiring limited mobility

STANDARD VINYL



Super Heavy Duty 450 lbs, Capacity, 2.5" High Resilient Density Foam for Better Comfort, Rubber Edge Banding Protection on Seat &

Model	Upholstery Type	Height Adjustment	Seat Dimensions	Back Dimensions	Footring	Base	Caster
<u>AL20S-V</u>	Vinyl	21"-31"	18" W x 18" D	15" W x 12" H	18"	Polished Aluminum	1
<u>AL22S-V</u>	Vinyl	17"-22"	18" W x 18" D	15" W x 12" H	NO	Polished Aluminum	1
<u>PL22S-V</u>	Vinyl	21"-31"	18" W x 18" D	15" W x 12" H	18"	Black Nylon	1
<u>PL22S-V</u>	Vinyl	17"-22"	18" W x 18" D	15" W x 12" H	NO	Black Nylon	1

COLOR OPTIONS

PreFixx Group II

• 100 Vinyl Face, Poly/cotton Backing, • Protective Coating for Increased Stain Resistence, • Abrasion 400,000 Double Rubs • Meets or Exceeds California Tech Bulletin 117, Boston Fire Dept. IX-1, • Federal Standard A-A-2950, • UFAC Fabric Class 1, • FMVSS-302

Blue-211	Navy-221	Burgundy-261	Black-251	Grey-231	Grey-232	Grey-233

MECHANISM OPTIONS



Controls	Description
DLC	Height and Back Tilt (This control has two levers for seat height and back angle adjustment and back height adjustment with knob
ST	Height and Seat and Back Tilt (This control has two levers, one for height adjustment and the other for Seat and Back tilt adjustment and back height with knob
FLC	Three Lever for Individual Lift (Height lever adjustment, seat tilt adjustment back tilt adjustment and height back adjustment with knob and a seat tension knob

FOOTRING OPTIONS



FR04	Knobless Nylon Footring 18" The Footring is Loosened and Tightened by Turning the Outer Ring. (option for models 20S, 45, 50 and 60)
FR05	Knobless Aluminum with Steel Ring 20" The Footring is Loosened and Tightened by Turning the Outer Ring. (option for models 10, 20M and 20W)
FR06	Nylon Center with Steel Ring, Footring 18" (option for models 20S, 45, 50 and 60)

ARM REST OPTIONS

2

		TF TA TA TA TA TA TA	
	Arms	Description	
	TF	Fixed Height and Width, Black	
	TA	Fixed Height and Adjustable Width, Black	
	TAA	Adjustable Height and Adjustable Width	
CA	ASTER OPT	IONS	
		B C C C C C C C C C C C C C C C C C C C	
	Caster	Description	
	1B	Braking Caster, Recommended where Chairs may roll to easily when is Not Occupied	
	1U	Soft Urethane Caster, Recommended on Tile, Cement and other Hard Surfaces	
	1UB	Soft Urethane Braking Caster, Recommended for reduce Mobility when is Not Occupied	

Nylon Glide, Recommended for use in areas where requiring limited mobility